

KAPPA

9682TOP200P63 CL67

EAN 4031582316063
Order number 00802588



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Kappa
Housing type	Swivel castor with total lock, head end of castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	1200 kg
Load capacity at 6 km/h	1000 kg
Load capacity Static	2000 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	80 °C
Overall height	245 mm
Overall width	116 mm
Overall weight	4.893 kg

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Natural white
Threadguards	With threadguard
Diameter	200 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (D)	75 Shore D

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Colour	Blue passivated
Offset	59 mm
Swivel radius	160 mm
Swivel interference	320 mm
Dome diameter	111 mm

FITTING

Fitting type	Rectangular plate
Plate length	135 mm
Plate width	110 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

KAPPA

9682TOP200P63 CL67

EAN 4031582316063
Order number 00802588



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

