

KAPPA

9681ITP160P63 CL67

EAN 4031582315592
Order number 00807242



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------------|
| Product name | Kappa |
| Housing type | Swivel castor with directional lock |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 1763.7 lb |
| Load capacity at 6 km/h | 1410.96 lb |
| Load capacity Static | 3527.39 lb |
| Temperature range (Minimum) | 14 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 8.07 in |
| Overall width | 4.33 in |
| Overall weight | 9.51 lb |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Aluminum |
| Tread material | Polyurethane, casted |
| Bearing | Precision ball bearing |
| Axle | Screwed with nut |
| Wheel color | Honey yellow (RAL1005) |
| Threadguards | With threadguard |
| Diameter | 6.3 in |
| Tread width | 1.97 in |
| Body width | 1.97 in |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 42 Shore D |

HOUSING

| | |
|---------------------|---|
| Material | Cast iron, or iron forged, heavy |
| Fork shape | Broad, reinforced |
| Swivel bearing | Two ball races, reinforced or stainless |
| Color | Blue passivated |
| Offset | 2.28 in |
| Swivel radius | 5.51 in |
| Swivel interference | 11.02 in |
| Dome diameter | 4.37 in |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 5.31 in |
| Plate width | 4.33 in |
| Plate hole length (Minimum) | 2.95 in |
| Plate hole length (Maximum) | 3.15 in |
| Plate hole width (Minimum) | 2.95 in |
| Plate hole width (Maximum) | 4.13 in |
| Plate hole diameter | 0.43 in |

KAPPA

9681ITP160P63 CL67

EAN 4031582315592
Order number 00807242



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

