

KAPPA

9688IEP160P63 CL67

EAN 4031582316414
Order number 00830646



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Kappa
Housing type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	350 kg
Load capacity at 6 km/h	280 kg
Load capacity Static	700 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall height	205 mm
Overall width	98 mm
Overall weight	3.416 kg

WHEEL

Body material	Aluminium
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Jet black (similar RAL9005)
Threadguards	With threadguard
Diameter	160 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (A)	68 Shore A

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Broad, reinforced
Colour	Blue passivated
Dome diameter	96 mm

FITTING

Fitting type	Rectangular plate
Plate length	135 mm
Plate width	110 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

KAPPA

9688IEP160P63 CL67

EAN 4031582316414
Order number 00830646



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

