

KAPPA

9681TOO100P63 CL67

EAN 4031582315622
Order number 00830523



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Kappa
Housing type	Swivel castor with directional lock
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	720 kg
Load capacity at 6 km/h	600 kg
Load capacity Static	1200 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall height	145 mm
Overall width	110 mm
Overall weight	3.472 kg

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Screwed with nut
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	100 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (D)	75 Shore D

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Colour	Blue passivated
Offset	41 mm
Swivel radius	95 mm
Swivel interference	190 mm
Dome diameter	111 mm

FITTING

Fitting type	Rectangular plate
Plate length	135 mm
Plate width	110 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

KAPPA

9681TOO100P63 CL67

EAN 4031582315622
Order number 00830523



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

