

PRODUCT INFORMATION

AGILA

 40 - 100 kg

 69 - 188 mm

 50 - 150 mm



TENTE

BETTER MOBILITY. BETTER LIFE.

AGILA

Full choice of customisable product solutions.



HOUSINGS

Pages: 4-9



WHEELS

Pages: 10-15



FITTINGS

Pages: 16-24

AGILA SMART

Selected standard products.



SMART VERSIONS

Pages: 25-31

BETTER MOBILITY IN PREMIUM QUALITY

TENTE believes in smart mobility solutions which noticeably improve people's lives and their work environment. TENTE solutions increase productivity, ensure safety and open up new horizons in matters of design and durability as well as environmental friendliness. Leading manufacturers and companies of different industries rely on these competencies and our high production quality.

On the following pages you will find technical information of our Agila product range. We will demonstrate the added value this mobility solution offers to your organisation. Among others:

Variable fitting options

Different fitting dimensions for a large range of applications.

User-friendly central lock

Simultaneous locking of more than one castor using a central actuation lever.

Certified conductivity

Conductive version to protect users and electrical devices from electrostatic discharge.

HOUSINGS



FEATURES



Optimised steering mechanism

Directional lock for improved steering around bends, as well as moving in a straight line over long distances.



User-friendly central lock

Simultaneous locking of more than one castor using a central actuation lever.



Secured stand

Total lock for swivel housing and locking the wheel simultaneously.




Painted surface

Black housing with bump and scratch resistant cathode immersion paint.



Compliant version

For use in commercial kitchens (DIN 18867 Part 8).



Resource-conserving part replacement

Threaded axles allow for effortless wheel change.

HOUSINGS

The housings are made of pressed steel, which is bright zinc plated and blue passivated. The wheel axle with nut makes it possible for an easy exchange of the wheel, resulting in reduced maintenance costs.

The Agila is also available in a stainless steel version or as twin wheel castor with increased manoeuvrability due to differential effect. Please contact us for more information.



Swivel castor

Swivel housing for easy manoeuvrability in all directions.



Wheel brake

Manually operated pedal lock prevents unintended movement.



Central directional and total lock

User-friendly central lock for simultaneous locking of more than one castor using a central actuation lever. Combined directional lock for improved steering around bends, as well as movement in a straight line over long distances. Also a total lock for simultaneously locking the wheel and swivel housing for a secure standing.



• **Central total lock**

User-friendly central lock for simultaneous locking of more than one castor using a central actuation lever. Total lock for simultaneously locking the wheel and swivel housing for a secure standing.



• **Directional lock**

Directional lock for improved steering around bends, as well as for moving in a straight line over a long distance.



• **Total lock**

The total lock simultaneously locks the wheel and swivel housing for a secure standing.



• **Fixed castor**

Wheel and housing are fixed for standard functionality. The castor is continuously aligned in the direction of travel.


Technical data and availability



Description	Housing type	Swivel castor	Swivel castor with wheel brake	Swivel castor with directional lock
	Article description	2470	2475	2471
	Material	Pressed steel	Pressed steel	Pressed steel
	Swivel bearing	Double ball bearing swivel head	Double ball bearing swivel head	Double ball bearing swivel head
Swivel interference	Wheel Ø 50 mm	98 mm	98 mm	-
	Wheel Ø 75 mm	123 mm	160 mm	-
	Wheel Ø 100 mm	176 mm	-	262 mm
	Wheel Ø 125 mm	207 mm	-	262 mm
	Wheel Ø 150 mm	240 mm	-	262 mm

Items with this sign "●" are available. Items with this sign "-" are not available in our standard range. Please contact us.

Swivel bearings



Two ball races for best manoeuvrability.



Swivel castor with central directional and total lock	Swivel castor with central total lock	Swivel castor with total lock	Fixed castor
2474	2476	2477	2478
Pressed steel	Pressed steel	Pressed steel	Pressed steel
Double ball bearing swivel head	Double ball bearing swivel head	Double ball bearing swivel head	-
-	-	-	●
-	-	160 mm	●
176 mm	176 mm	262 mm	●
207 mm	207 mm	262 mm	●
240 mm	240 mm	262 mm	●



Washability

The Agila is also available in a stainless steel version for washability. Please contact us for more information.




Optimised manoeuvrability

The Agila is also available as a twin wheel castor with high manoeuvrability due to differential effect. Please contact us for more information.

WHEELS



FEATURES




Low-vibration transport

Extra soft wheels with good shock-absorbing properties.



Sterile cleaning

Wheels for steam sterilisation in autoclaves used in sterile areas.




Constant heat resistance

Duratech wheels made of heat resistant material for use in extreme environments.



Protective seal

Wheels with sealed bearings to protect against water spray and dirt.




Quiet rolling

Soft wheel versions for a quiet working environment.



Non-marking movement

Wheels with reduced abrasion and minimal cleaning effort.




Non-staining operation

Non-staining on contact with floors when left standing for long periods.



Low-maintenance wheels

Thread guards for unobstructed operation with minimal cleaning effort.



Certified conductivity

Conductive version to protect users and electrical devices from electrostatic discharge.

WHEELS

The characteristics of our wheel range are as diverse as their uses. Precisely adapted to the required parameters, they provide optimal manoeuvrability with perfectly matched components, even under the most extreme conditions. You'll discover a wide range of wheels in our Agila product range. Here are the four wheel types.



• **Puretech**
Robust wheel with rubber tread for versatile use. Protection through low-vibration transport. An electric conductive version is also available.



• **Supratech**
All-around smooth-running wheel with thermoplastic rubber tread. Excellent performance in manoeuvrability and mobility due to the use of high-performance material. A washable and electric conductive version is also available.



Maxtech

Perfect for a functional design, injection-moulded polyurethane. Optimal material properties for any purpose. An electric conductive version is also available.



Duratech

Stable and indestructible, made of polyamide and thermosetting plastic with an abrasion-resistant tread.



Wide range

See our full range of wheels on the following pages.

Technical data and availability

ELECTRIC
CONDUCTIVE

	Puretech	Puretech precision	Puretech steel	Puretech conductive	Supratech
Product name	PIO	PIP	DIK	DYK	PJI
Article description	PIO	PIP	DIK	DYK	PJI
Tread material	Solid rubber, grey non-marking	Solid rubber, grey non-marking	Solid rubber, grey non-marking	Solid rubber, black non-staining	Thermoplastic rubber, grey non-marking
Tread hardness	Shore A 80	Shore A 75	Shore A 80	Shore A 80	Shore A 87
Wheel body material	Polypropylene	Polypropylene	Pressed steel	Pressed steel	Polypropylene
Thread guard	-	-	● Pressed steel	● Pressed steel	-
Temperature range	-20 °C / +60 °C	-20 °C / +60 °C	-20 °C / +85 °C	-20 °C / +85 °C	-20 °C / +60 °C
Width of tread in mm / wheel diameter in mm	- 25 / Ø 75 32 / Ø 100 - 150	- 25 / Ø 75 32 / Ø 100 - 150	19 / Ø 50 25 / Ø 75 32 / Ø 100 - 150	19 / Ø 50 25 / Ø 75 32 / Ø 100 - 150	19 / Ø 50 25 / Ø 75 32 / Ø 100 - 150
Electric conductive (10⁴ OHM)	-	-	-	●	-
Plain bearing	●	-	-	-	●
Roller bearing	-	-	-	-	-
Cone ball bearing	-	-	●	●	-
Precision ball bearing	-	●	-	-	-
Wheel Ø 50 mm	-	-	40 kg	40 kg	40 kg
Wheel Ø 75 mm	60 kg	60 kg	55 kg	55 kg	-
Wheel Ø 100 mm	60 kg	80 kg	80 kg	80 kg	-
Wheel Ø 125 mm	80 kg	100 kg	100 kg	100 kg	-
Wheel Ø 150 mm	80 kg	80 kg	100 kg	100 kg	-

Items with this sign "●" are available. Items with this sign "-" are not available in our standard range. Please contact us. The mentioned load capacity is only valid for the Agila pressed steel single wheel castors.

Bearing types



Plain bearing for short distances.



Cone ball bearing provides improved rolling properties.



Precision ball bearing for highest performance.

ELECTRIC CONDUCTIVE				ELECTRIC CONDUCTIVE		
Supratech precision	Supratech conductive	Maxtech precision	Maxtech	Maxtech conductive	Duratech	Duratech
PJP	YGO	UAP	UAK	XSP	UOO	UOK
Thermoplastic rubber, grey non-marking	Thermoplastic rubber, grey non-marking	Polyurethane	Polyurethane	Polyurethane	Polyamide	Polyamide
Shore A 85	Shore A 85	Shore D 40	Shore D 40	Shore D 40	Shore D 75	Shore D 75
Polypropylene	Polypropylene	Polyamide	Polyamide	Polyamide	Polyamide	Polyamide
● Polypropylene	-	● Polyamide	● Pressed steel	● Polyamide	-	● Pressed steel
-20 °C / +60 °C	-20 °C / +60 °C	-40 °C / +80 °C	-40 °C / +80 °C	-40 °C / +80 °C	-40 °C / +80 °C	-40 °C / +80 °C
- 25 / Ø 75 32 / Ø 100 - 150	19 / Ø 50 25 / Ø 75 32 / Ø 100 - 125	20 / Ø 50 - 32 / Ø 100 - 150	20 / Ø 50 - -	- - 32 / Ø 100 - 150	20 / Ø 50 - -	19 / Ø 50 - -
-	●	-	-	●	-	-
-	●	-	-	-	●	-
-	-	-	-	-	-	-
-	-	-	●	-	-	●
●	-	●	-	●	-	-
-	50 kg	40 kg	50 kg	-	50 kg	50 kg
75 kg	75 kg	-	-	100 kg	-	-
100 kg	80 kg	100 kg	-	100 kg	-	-
100 kg	100 kg	100 kg	-	100 kg	-	-
100 kg	-	100 kg	-	100 kg	-	-



Load capacity

The load capacity depends on the housing and wheels. Each has been tested and fulfills the requirements according to EN 12528 and EN 12530 at a speed of 4 km/h. When using four castors, you can calculate the necessary load capacity as follows: The sum of the weight of your application plus the additional load divided by three castors.

$$\frac{\text{Weight of application} + \text{load}}{3} = \text{Load capacity of one castor}$$



Temperature range

Castors with an expander fitting have a lower temperature range of -10 °C / +40 °C.

FITTINGS



FEATURES



Variable fitting options

Different fitting dimensions for a large range of applications.



Fast assembly

Faster assembly process through the use of plug-in fittings.

ADDITIONAL FEATURES



Practical system solution

Practical system solution with all the technical components for central locking.



Colour matching

Colours can be adapted to match the product design.



Non-hazardous materials

Complies with the RoHS directive and REACH regulation of the European Union. Does not contain polycyclic aromatic hydrocarbons or chromium (VI).



Tested quality

Tested in our own laboratory for compliance with European standards.

PLATE FITTINGS

The fitting of a castor is dependent on the application it's being attached to. With plate fittings, the castors can be screwed under the device with four screws. This ensures a simple and robust connection.



Fixed plates P50
The longside of plate is 90° in the direction of travel.

Technical data and availability

						
Description	Fitting type	Swivel plate	Fixed plate	Swivel plate	Fixed plate	Fixed plate
	Article description	P40	P41	P50	P50	P60
	Size of plate	60 x 60 mm	55 x 55 mm	77 x 67 mm	77 x 67 mm	67 x 60 mm
	Plate hole centres in mm	48/38 x 48/38	44/38,5 x 44/38,5	61,5/56 x 51,5/46,5	61,5/56 x 51,5/46,5	48/40 x 48/40
	Plate hole Ø	6,3 mm	6,3 mm	8,5 mm	8,5 mm	6,3 mm
Overall height	Wheel Ø 50 mm	69 mm	69 mm	-	-	-
	Wheel Ø 75 mm	100 mm	-	-	-	100 mm
	Wheel Ø 100 mm	-	-	135 mm	135 mm	-
	Wheel Ø 125 mm	-	-	160 mm	160 mm	-
	Wheel Ø 150 mm	-	-	185 mm	185 mm	-

Items with this sign "-" are not available in our standard range. Please contact us.





BOLT HOLE FITTINGS

A bolt hole offers the option to fix the application to the castor with a standard screw M10 or M12. Screws of any length can be used.

Bolt hole  For screws of any length.




Technical data and availability

			
Description 	Fitting type	Bolt hole	Bolt hole
	Article description	P30-11	P30-13
	Bolt hole Ø	11 mm	13 mm
Overall height 	Wheel Ø 50 mm	69 mm	-
	Wheel Ø 75 mm	100 mm	-
	Wheel Ø 100 mm	135 mm	135 mm
	Wheel Ø 125 mm	160 mm	160 mm
	Wheel Ø 150 mm	185 mm	185 mm





Items with this sign "-" are not available in our standard range. Please contact us.

SOLID STEM FITTINGS

For easy mounting into tubes, we offer solid stem fittings with suitable adaptors. All fittings are made with high quality bright zinc plating and blue passivated to ensure long-lasting use.



Technical data and availability

				 CENTRAL LOCKING	
Description	Fitting type	Solid stem	Solid stem	Solid stem with central total and directional lock	Solid stem with central total and directional lock
	Article description	R05-28	R05-32	R26-28	R36-32
	Thread for fixation screw	M8	M8	4 x M8	4 x M6
	Thread position from bottom	19 mm	19 mm	19 mm	7 mm
	Solid stem \varnothing	28 mm	32 mm	28 mm	32 mm
	Solid stem length	45 mm	45 mm	96 mm	50 mm
	Shifting angles for actuation forces	-	-	2 x 45°	2 x 30°
Overall height	Wheel \varnothing 50 mm	-	-	-	-
	Wheel \varnothing 75 mm	-	-	-	-
	Wheel \varnothing 100 mm	138 mm	138 mm	138 mm	138 mm
	Wheel \varnothing 125 mm	163 mm	163 mm	163 mm	163 mm
	Wheel \varnothing 150 mm	188 mm	188 mm	188 mm	188 mm

Items with this sign "-" are not available in our standard range. Please contact us.


ADAPTORS FOR TUBES

For a flexible mounting in square tubes, an adaptor is available for solid stem fittings.




Technical data and availability



Description	 Tube type	Square
	Article description	R48
	Compatible with product	R05-28
	Adaptor measurements	33,65 x 33,65 mm 36 x 36 mm
	Solid stem \varnothing	28 mm
	Solid stem length	45 and 60 mm

EXPANDING FITTINGS FOR TUBES

For an easy mounting into tubes, we offer for bolt hole fittings suitable expanding fittings. The adjustable expanders allow for flexible installation in different tube sizes.



Technical data and availability

				
Description 	Fitting type	Bolt hole	Expander, round	Expander, square
	Article description	P30-11	R07	R47
	Bolt hole Ø	11 mm	-	-
	Compatible with	R07 and R47	P30-11	P30-11
	Expander measurements	-	Ø 19 - 21,5 mm Ø 21,5 - 24 mm Ø 24 - 27 mm Ø 27 - 30 mm Ø 31 - 35 mm	Ø 21,5 - 24 mm Ø 24 - 27 mm Ø 27 - 30 mm Ø 32 - 35 mm Ø 36 - 40 mm
Overall height 	Wheel Ø 50 mm	69 mm	-	-
	Wheel Ø 75 mm	100 mm	103 mm	103 mm
	Wheel Ø 100 mm	135 mm	138 mm	138 mm
	Wheel Ø 125 mm	160 mm	163 mm	163 mm
	Wheel Ø 150 mm	185 mm	188 mm	188 mm



Expander fittings

Our expanders and castors can be delivered separately or completely assembled. Castors with an expander fitting have a lower temperature range of -10 °C / +40 °C.

Items with this sign "-" are not available in our standard range. Please contact us.



STEM FITTINGS

These fittings are installation-friendly and provide additional safety due to the circlip.



Technical data and availability




 Description	Fitting type	Stem with circlip
	Article description	B10
	Stem measurements	11 x 31 mm
	Stem \varnothing	11 mm
 Overall height	Wheel \varnothing 50 mm	72 mm
	Wheel \varnothing 75 mm	103 mm
	Wheel \varnothing 100 mm	-
	Wheel \varnothing 125 mm	-

Items with this sign "-" are not available in our standard range. Please contact us.

SOCKETS

Different sockets are available for castors with a stem fitting.



Technical data and availability



i Description	Tube type	Round	Square	Round (wooden furniture)
	Article description	R20	R40	H40
	Compatible with	B10	B10	B10
	Socket \varnothing / collar \varnothing	14/18 mm 15/18 mm 16/18 mm 17/19 mm 18/20 mm 19/21 mm 20/21 mm 22/25 mm 23/26 mm	16/20 mm 17/19 mm 18/20 mm 21/23,5 mm 22/24,5 mm 23/25,5 mm 26/30 mm	15 mm
	Overall height	36 mm	36 mm	36 mm

AGILA SMART



AGILA SMART

The Agila also has a smart version available. These are selected standard products with less load capacity. There are two different housing types available.


AGILA SMART FOR LOADS UP TO 70 KG

Housing versions



Description	Housing type	Swivel castor	Swivel castor with wheel brake	Swivel castor with total lock
	Article description	1470	1475	1477
	Material	Pressed steel	Pressed steel	Pressed steel
	Swivel bearing	Double ball bearing swivel head	Double ball bearing swivel head	Double ball bearing swivel head
Swivel interference	Wheel Ø 50 mm	100 mm	128 mm	-
	Wheel Ø 75 mm	125 mm	-	156 mm
	Wheel Ø 100 mm	156 mm	-	174 mm
	Wheel Ø 125 mm	201 mm	-	-
	Wheel Ø 150 mm	-	-	-

Swivel bearing



Precision ball bearing for best manoeuvrability.

Items with this sign "-" are not available in our standard range. Please contact us.

Wheel versions



i		Maxtech	Basetech	Basetech
Description	Product name	PAO	POI	POO
	Article description	Polyurethane	Polypropylene	Polypropylene
	Tread material	Shore D 40	Shore D 65	Shore D 65
	Tread hardness	Polypropylene	Polypropylene	Polypropylene
	Wheel body material	-	-	-
	Thread guard	-20 °C / +60 °C	-20 °C / +60 °C	-20 °C / +60 °C
	Temperature range	19 / Ø 50 25 / Ø 75 - 100	18 / Ø 50	18 / Ø 50 25 / Ø 75 - 100
	Width of tread in mm / wheel diameter in mm	-	-	-
	Electric conductive (10 ⁴ OHM)	●	●	●
Bearing type	Plain bearing	-	-	-
	Roller bearing	-	-	-
	Cone ball bearing	-	-	-
	Precision ball bearing	-	-	-
Load capacity	Wheel Ø 50 mm	40 kg	40 kg	40 kg
	Wheel Ø 75 mm	60 kg	-	40 kg
	Wheel Ø 100 mm	70 kg	-	70 kg
	Wheel Ø 125 mm	-	-	-
	Wheel Ø 150 mm	-	-	-

Bearing type



Plain bearing for short distances.

Items with this sign "●" are available. Items with this sign "-" are not available in our standard range. Please contact us. The mentioned load capacity is only valid for the Agila smart castors for loads up to 70 kg.



Load capacity



The load capacity depends on the housing and wheels. Each has been tested and fulfills the requirements according to EN 12530 at a speed of 4 km/h. When using four castors, you can calculate the necessary load capacity as follows: The sum of the weight of your application plus the additional load divided by three castors.

$$\frac{\text{Weight of application + load}}{3} = \text{Load capacity of one castor}$$

Fitting versions

Plate fittings



Description	 Fitting type	Swivel plate	Swivel plate
	Article description	P40	P50
	Size of plate	60 x 60 mm	77 x 67 mm
	Plate hole centres in mm	48/38 x 48/38	61,5/56 x 51,5/46,5
	Plate hole \varnothing	6,3 mm	8,5 mm
Overall height	 Wheel \varnothing 50 mm	70 mm	-
	Wheel \varnothing 75 mm	100 mm	-
	Wheel \varnothing 100 mm	-	125 mm
	Wheel \varnothing 125 mm	-	-
	Wheel \varnothing 150 mm	-	-

Items with this sign "-" are not available in our standard range. Please contact us.




Fixed castors

Please contact us if you are interested in fixed castors.

Bolt hole fittings



Description	 Fitting type	Bolt hole
	Article description	P30-11
	Bolt hole \varnothing	11 mm
Overall height	 Wheel \varnothing 50 mm	70 mm
	Wheel \varnothing 75 mm	100 mm
	Wheel \varnothing 100 mm	125 mm
	Wheel \varnothing 125 mm	-
	Wheel \varnothing 150 mm	-

Items with this sign "-" are not available in our standard range. Please contact us.


AGILA SMART FOR LOADS UP TO 80 KG

Housing versions



Description	i			
	Housing type	Swivel castor	Swivel castor with total lock	
	Article description	1670	1677	
	Material	Pressed steel	Pressed steel	
Swivel bearing	Double ball bearing swivel head	Double ball bearing swivel head		
Swivel interference	↻	Wheel Ø 50 mm	-	-
	↻	Wheel Ø 75 mm	-	-
	↻	Wheel Ø 100 mm	176 mm	233 mm
	↻	Wheel Ø 125 mm	207 mm	233 mm
	↻	Wheel Ø 150 mm	-	-

Swivel bearing



Precision ball bearing for best manoeuvrability.

Items with this sign "-" are not available in our standard range. Please contact us.

Wheel versions



Description	Product name	Puretech	Puretech precision	Supratech	Supratech precision
	Article description	PIO	PIP	PJO	PJP
	Tread material	Solid rubber, grey non-marking	Solid rubber, grey non-marking	Thermoplastic rubber, grey non-marking	Thermoplastic rubber, grey non-marking
	Tread hardness	Shore A 80	Shore A 75	Shore A 88	Shore A 85
	Wheel body material	Polypropylene	Polypropylene	Polypropylene	Polypropylene
	Thread guard	-	● Polypropylene	-	● Polypropylene
	Temperature range	-20 °C / +60 °C	-20 °C / +60 °C	-20 °C / +60 °C	-20 °C / +60 °C
	Width of tread in mm / wheel diameter in mm	32 / Ø 100 - 125	32 / Ø 100 - 125	32 / Ø 100 - 125	32 / Ø 100 - 125
	Electric conductive (10 ⁴ OHM)	-	-	-	-
Bearing type	Plain bearing	●	-	●	-
	Roller bearing	-	-	-	-
	Cone ball bearing	-	-	-	-
	Precision ball bearing	-	●	-	●
Load capacity	Wheel Ø 50 mm	-	-	-	-
	Wheel Ø 75 mm	-	-	-	-
	Wheel Ø 100 mm	60 kg	70 kg	80 kg	70 kg
	Wheel Ø 125 mm	80 kg	80 kg	80 kg	80 kg
	Wheel Ø 150 mm	-	-	-	-

Items with this sign "●" are available. Items with this sign "-" are not available in our standard range. Please contact us. The mentioned load capacity is only valid for the Agila smart for loads up to 80 kg.



Load capacity

The load capacity depends on the housing and wheels. Each has been tested and fulfills the requirements according to EN 12530 at a speed of 4 km/h. When using four castors, you can calculate the necessary load capacity as follows: The sum of the weight of your application plus the additional load divided by three castors.

$$\frac{\text{Weight of application} + \text{load}}{3} = \text{Load capacity of one castor}$$

Bearing types



Plain bearing for short distances.



Precision ball bearing for highest performance.

Fitting versions

Plate fittings



Description	Fitting type	Swivel plate
	Article description	P50
	Size of plate	77 x 67 mm
	Plate hole centres in mm	61,5/56 x 51,5/46,5
	Plate hole \varnothing	8,5 mm
Overall height	Wheel \varnothing 50 mm	-
	Wheel \varnothing 75 mm	-
	Wheel \varnothing 100 mm	135 mm
	Wheel \varnothing 125 mm	160 mm
	Wheel \varnothing 150 mm	-

Items with this sign "-" are not available in our standard range. Please contact us.



Fixed castors

Please contact us if you are interested in fixed castors.

Bolt hole fittings



Description	Fitting type	Bolt hole
	Article description	P30-13
	Bolt hole \varnothing	13 mm
Overall height	Wheel \varnothing 50 mm	-
	Wheel \varnothing 75 mm	-
	Wheel \varnothing 100 mm	135 mm
	Wheel \varnothing 125 mm	160 mm
	Wheel \varnothing 150 mm	-

Items with this sign "-" are not available in our standard range. Please contact us.


DIVERSITY WITH A SYSTEM

OUR CASTORS

All of our products have their own specific qualities and strengths. Whether it's high design standards, specialist applications or exceptional load capacities – our range can meet your needs and can be adapted to fit different models.

From the correct dimensions and technical specifications to the required configuration, our product families are able to offer the ideal solution – whatever you need. Contact us for more information or visit our website: www.tente.com

E-Drive



⌀ 125 mm

Alpha



⊃ 70 - 500 kg
⌀ 80 - 200 mm

Delta



⊃ 300 - 600 kg
⌀ 125 - 200 mm

Delta twin



⊃ 600 - 750 kg
⌀ 125 - 200 mm

Zeta



⊃ 300 - 800 kg
⌀ 125 - 250 mm

Kappa



⊃ 300 - 2.000 kg
⌀ 80 - 300 mm

Kappa flex




⊃ 360 - 750 kg
⌀ 160 - 200 mm

Omikron



⊃ 900 - 11.000 kg
⌀ 100 - 500 mm

Radiata



1.200 - 1.500 kg
80 mm

Scout



150 - 350 kg
160 - 200 mm

Integral



100 - 150 kg
100 - 200 mm

Integral twin



125 - 250 kg
100 - 150 mm

Linea clinic



150 - 200 kg
125 - 150 mm

Aviana care



100 kg
75 mm

Aviana



75 mm

Agila



40 - 100 kg
50 - 150 mm

Agila twin



50 - 100 kg
50 - 75 mm

Stora



60 - 160 kg
75 - 160 mm

Mono



30 - 70 kg
50 - 100 mm

Galea



60 - 100 kg
100 - 125 mm

Levina



60 - 100 kg
75 - 150 mm

Linea



40 - 150 kg
50 - 150 mm

Anika



40 - 50 kg
55 - 75 mm

Lumina



30 - 100 kg
35 - 75 mm

Stylea



40 - 100 kg
35 - 100 mm

Smiles



40 kg
50 mm

Compacta



10 - 55 kg
14 - 50 mm

EXPERTISE THAT INSPIRES

CONTACT US

We are a globally operating company supporting you on five continents. This means on-site support with service on a level playing field – along with in-depth knowledge. Additionally, our solution experts will advise you on the best mobility concept for your needs. Go here to find your nearest TENTE location: www.tente.com/locations

INCREASE YOUR EFFICIENCY

Our intelligent mobility solutions help you save time, effort, energy, and operating expenses. This allows you to improve your operating methods and working conditions, thereby optimising your processes and ensuring higher productivity, profitability and safety. Ask for our solutions catalogue or read about how our customers benefit from our tailor-made solutions on our website: www.tente.com/solutions


SAVE DEVELOPMENT TIME

On our website you will find technical drawings, product data sheets and 2D and 3D CAD files in various formats: www.tente.com/agila

GET MORE INFORMATION

In addition to our informative website, you can easily download various catalogues and brochures on mobility solutions, customer references, and much more: www.tente.com/download





www.tente.com



PRODUCTIVITY



SAFETY



DESIGN



DURABILITY



ENVIRONMENT